# Overview Accessories for KombiSIGN

## KombiSIGN 70 and 71




















Cable 5 m with M12 connector and plug Order no. 960 000 46 Cable 5 m with M12 plug Order no. 960 000 47 Cable 5 m with M12 connector Order no. 960 860 01



### Interface box and terminal element for KombiSIGN 71

(only for the permanent light element 641 X00 00 and corresponding light bulb (24V))
Interface box and terminal element
Interface box and terminal element

with 2 cable glands M16
Order no. 960 000 16



Drive: Interfaces: Assembly: Interface box and terminal element with 1 cable glands M16 and assembly Order no. 960 000 17

24 V DC RS 232, RS 485

Network appliance with cable, connecting cable RS 232, 2 m long with Sub-D 9-pin and socket for power supply, CD with demonstration programme, programming handbook

# Overview Accessories KombiSIGN

## KombiSIGN 50, 70 and 71

Contact box for cable exit at side, with mounting material and seal, cable gland M16 x 1.5 Order no. 975 840 01



Contact box with magnetic base and cable exit at side cable gland M16 x 1.5

Order no. 975 840 04



Bracket for tube mounting, incl. cable gland M16 x 1.5 **Order no. 960 000 01** 



Base for tube mounting,  $\emptyset$  25 mm, plastic, incl. rubber seal **Order no. 975 840 90** 



Base for tube Ø 25 mm, metal, incl. rubber seal, recommended for tube lengths of 400 mm and longer **Order no. 975 840 91** 



Bracket for base mounting, with concealed cable entry, incl. rubber seals

Order no. 960 000 14



Corner fixing bracket
Order no. 960 000 41



Tube  $\emptyset$  25 mm, all anodized aluminium 100 mm long **975 845 10** 

250 mm long 975 840 25 400 mm long 975 840 40 600 mm long 975 840 60 800 mm long 975 840 80 1000 mm long 975 840 03



Indication board (for tube mounting) Order no. 960 000 05



- For one to five modules
- Simple mounting onto signal tower tube
- Ample space for written information
- Simply break off unwanted segments

LED bulb BA15d total length max. 42 mm Colours: red, yellow, green, clear, blue Voltage 24 V, 115 V, 230 V Order specifications see page 185



Bulb BA15d, total length max. 42 mm

12 V, 5 Watt 955 840 34 24 V, 5 Watt 955 840 35 30 V, 5 Watt 955 840 32 115 V, 5 Watt 955 840 38




Dimensions of indication board (W x H):  $153 \times 345 \text{ mm}$ 

Surface area per section (W x H): c. 144 x 54 mm, e.g. Zweckform 3424 (105 x 48 mm), Herma 4281 (105 x 50.8 mm) (not included in assembly)

Material: PMMA



## KombiSIGN 50, 70 and 71



Order no. 960 000 30



**Dimensions** (Ø x Height): 70

Material:
Cable diameter:

70 mm x 117 mm PA-GF

Max. 14 mm

Vertical, horizontal, Positioning in 7,5° steps

#### QUICK AND SIMPLE MOUNTING:



Fixina:

Place the lower part of the Foldaway Base in the desired position



Attach the upper part directly onto the signal tower tube. Insert the connection cable



Place the upper and lower parts together at the desire angle



Place the upper and lower parts together at the desired angle

Tube Ø 25 mm, plastic, 45 mm long, for direct mounting of the Terminal Element onto the Foldaway Base (only for Kombi*SIGN* 70 and 71)

Order no. 960 000 31



## NEW

Foldaway Base - Signal Tower can be folded away, including rubber seal, for tube (all anodized aluminium)  $\emptyset$  25 mm (not included in assembly)

Order no. 960 009 12



**Dimensions** (Ø x Height): 70 mm x 85 mm

Material: Cable diameter: Fixina: PA-GF

Max. 8 mm Vertical, horizontal,

Positioning in 0° and 90°

#### QUICK AND SIMPLE MOUNTING:



Place the "foldaway' base in the desired mounting position



Attach the tube adaptor directly to the signal tower and introduce the cable



Fix the whole assembly - tube adaptor and signal tower, in the desired position, vertically or horizontally - onto the foldaway base



Tube Ø 25 mm, plastic, 45 mm long, for direct mounting of the Terminal Element onto the Foldaway Base

(only for Kombi*SIGN* 70 and 71) **Order no. 960 000 31** 



## KombiSIGN 50







### **TECHNICAL DIAGRAMS:**

see page 327 onwards